

UltraPure, Low-Flow Cleaning

Alfa Laval TJ SaniMidget SB UltraPure Rotary Spray Head

Application

The Toftejorg SaniMidget SB UltraPure Rotary Spray Head is with its 3A approval, preliminary designed for the dairy industry with respect to self-cleaning, self-draining and inspectability. Its novel patent pending one-clip assembly offers easy installation, disassembly and inspection without compromising cleanability or drainability. Sizing/selection and installation drawings are available. Contact Alfa Laval for recommendations.

Working Principles

The flow of cleaning media causes the head of the SaniMidget SB UltraPure to rotate, with fans of water laid out in a swirling pattern on the entire perimeter exposed to the spray pattern. This generates a vibrating impact in the 270° upward pattern and a dynamic cascading flow that covers internal surfaces of the tank, vessel or reactor. The SaniMidget SB UltraPure is designed according to EHEDG and the design meets the requirements of 3-A standards.



TECHNICAL DATA

Lubricant: Lubrication by rinse/cleaning fluid
 Wetting radius: Max. 3 m
 Impact cleaning radius: Max. effective 1.4 m

Pressure

Working pressure: 1-3 bar
 Recommended pressure: 2 bar

Spray Pattern



360°



270° up

Standard Design

The SaniMidget SB UltraPure can be supplied with 3.1 certificates for metallic parts and FDA conformity and USP Class IV on non-metallic parts.

Certificates

2.2 material certificate and EHEDG
 As add-on: Q-doc, Q-doc incl. FAT & SAT and ATEX.

PHYSICAL DATA

Materials

Metallic parts: AISI 316L (UNS S31603)
 Non-metallic parts: PEEK MG

Surface finish Ra < 0.8µm
 Steam or gas (air): Not supported - Contact Alfa Laval

Temperature

Max. working temperature: . . . 95°C
 Max. ambient temperature: . . . 150°C

Weight: 1": 0.20 kg

Connections

- Weld-on: 1" ISO 2037, or DN25 DIN11850-R1, or 1" BPE US
- Clip-on: 1" BPE US

Clip-on options

Easy-on/off clip (ø4.0 mm). (Clip needed for both clip-on and weld-on versions to assemble the machine)

